

Date: May 23, 2014

To: ASTM Testing Laboratories

From: Jason Bowden / OH Technologies, Inc.

Re: CPD Technical Memo 25
OHT6A-012-2 Housing, Oberg, 6" w/ 60 micron filter
OHT6A-012-3 Housing, Oberg, 6" w/ 28 micron filter

Cc: Mr. Rich Grundza/ Test Monitoring Center

This Technical Memo is intended to notify users of the ASTM Testing Methods that utilize OHT part numbers OHT6A-012-2 and OHT6A-012-3 Oberg Housings of a part design change. The manufacturer of the Oberg housings will no longer produce the 2 port version that is currently in use. The new design is a 4 port version (2 IN & 2 OUT) to offer better installation flexibility. These housings will ship with 2 threaded plugs to be installed in the ports that are not utilized. The new Oberg housing version has an increase in volume of 34ml.

The new OHT part numbers will be as follows:

OHT6A-012-4	Housing, Oberg, 6" w/ 60 micron filter and 2 each threaded port plugs
OHT6A-012-5	Housing, Oberg, 6" w/ 28 Micron filter and 2 each threaded port plugs

If there are any questions or comments regarding the aforementioned item please do not hesitate to contact me.

Jason H. Bowden
OH Technologies, Inc.